

Technical data sheet

Adjustable insulating beam – pipe

Item number: 5408849



Insulated spacer for cables and air-termination rods for insulated air-termination devices, to maintain the separation distance. Infinitely adjustable distance range. For mounting with tightening strap on pipes with $\varnothing \leq 600$ mm. Including tension jack.



Fibre-glass-reinforced plastic

Master data

Item number	5408849
Type	ISAV1000R
Description 1	Insulated spacer
Description 2	variable length adjustment
Manufacturer	OBO
Dimension	550-1000mm
Material	Fibre-glass-reinforced plastic
Smallest sales unit	1
Unit of quantity	Piece
Weight	130 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	6,1768 kg CO2e / 1 Piece

Technical data sheet

Adjustable insulating beam – pipe

Item number: 5408849



Dimensions

