

Technical data sheet

Combination nut DIN 6923 V2A

Item number: 3156122



Combination nut with pressed washer in accordance with EN 1661.



A2 Stainless steel

2B Bright, treated

Master data

Item number	3156122
Type	KM M10 A2
Description 1	Hexagonal nut with flange
Description 2	with underhead tothing
Manufacturer	OBO
Dimension	M10
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	50
Unit of quantity	Piece
Weight	1.32 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,0635 kg COe / 1 Piece


Technical data sheet

Combination nut DIN 6923 V2A

Item number: 3156122



Dimensions



Dimension d	21.8 mm
Dimension h	10 mm

Technical data

Thread	M10
Thread metric	10
Thread type	Metric
Halogen-free	yes
With flange	yes
WAF	15
Self-locking	no
Left thread	no
Thread, imperial	7/16"
Nut version	Nut
Screw system nut	Hexagon head