


Technical data sheet

Magic straight connector set DD

Item number: 6069034



Cable tray connector with quick fastening for the screwless connection of perforated cable trays with a side height of 85 mm.
The optimised design means that the connector can be used to create radii and as a length compensation piece for large temperature deviations.



St

Steel

DD

Strip galvanised zinc/aluminium, Double Dip

Master data

Item number	6069034
Type	KTSMV 850 DD
Description 1	Straight connector set
Description 2	for cable tray Magic
Manufacturer	OBO
Dimension	85x500x200
Colour	zinc
Material	Steel
Surface	Strip galvanised zinc/aluminium, Double Dip
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	64 kg
Weight unit	kg/100 pc.


Technical data sheet

Magic straight connector set DD


Item number: 6069034



Dimensions



Dimension	85x500
Length	200 mm
Width	500 mm
Height	85 mm
Plate thickness	1 mm
Dimension B	500 mm



Technical data

Version for	Straight connector
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Suitable for cable tray system height	85 mm
Adjustable connector, horizontal	no
Articulated connector, vertical	no
Rustproof steel, pickled	no
Connection type	Screwless connector