

Technical data sheet

Adjustable bend element 110 FS

Item number: 6225494



Adjustable bend element with welded rung for use in the cable ladder types with a side height of 110 mm.



- St

Steel
- FS

Strip galvanized

Master data	
Item number	6225494
Description 1	Adjustable bend element
Description 2	for cable ladder
Manufacturer	OBO
Dimension	110x400
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	155.3 kg
Weight unit	kg/100 pc.


Technical data sheet

Adjustable bend element 110 FS

Item number: 6225494



Dimensions



Width	400 mm
Height	110 mm
Dimension B	400 mm
Dimension R	400 mm

Technical data

Bend (angle)	Adjustable
Version of the rungs	Profile perforated
Side rail version	Flat profile
Connector version	Integrated connector
Maintain electrical functions	no
Change of direction	Vertical, rising/falling
Rustproof steel, pickled	no
Hinged	yes
Side perforation	no
Wide-span version	no
Rail thickness	1.5 mm