

Technical data sheet

T piece, for cable trunking type LKM 60200

Item number: 6248225



T piece including cover for changing the direction of the LKM trunking.
Equipotential bonding without additional aids, between base and cover



St	Steel
FS	Strip galvanized

Master data

Item number	6248225
Type	LKM T60200FS
Description 1	T piece
Description 2	with cover
Manufacturer	OBO
Dimension	60x200mm
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	106 kg
Weight unit	kg/100 pc.

Technical data sheet


T piece, for cable trunking type LKM 60200

Item number: 6248225



Dimensions

Length	300 mm
Width	200 mm
Height	64 mm
Dimension a	300 mm



Technical data

Departing width	200 mm
Departing height	64 mm
Version for	Base and cover
Fastening type	Base perforation
Maintain electrical functions	no
for duct dimension	60 x 200
Halogen-free	yes
Duct height, min.	64 mm
Trunking depth	64 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK10
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C