

Technical data sheet

T piece 60 A4

Item number: 6225274



T piece, horizontal, with welded rung for all cable ladder types of 60 mm side height.
Connectors should be ordered separately and in the appropriate quantity.



A4 Stainless steel

2B Bright, treated

Master data

Item number	6225274
Description 1	T piece
Description 2	for cable ladder
Manufacturer	OBO
Dimension	60x400
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	635.6 kg
Weight unit	kg/100 pc.

Dimensions

Width	400 mm
Height	60 mm
Dimension B	400 mm
Dimension R	300 mm

Technical data sheet

T piece 60 A4

Item number: 6225274



Technical data

Version of the rungs	Profile unperforated
Side rail version	Flat profile
Connector version	Without connectors
Type	Exit symmetrical
Maintain electrical functions	no
Rustproof steel, pickled	no
Wide-span version	no
Rail thickness	1.5 mm