

# Technical data sheet

## Central hanger for cable tray, side height 60 mm FS

Item number: 6358717



Centre suspension for cable trays with rolled side rail of side height 60 mm. The centre suspension possesses a rotatable M10 threaded sleeve. When filling, ensure an even distribution of the load (avoid one-sided filling).

The widths 100, 150 and 200 mm have additional base perforations, in order to screw the centre suspensions to the tray base when used for the maintenance of electrical functionality according to DIN 4102 Part 12.



**St** Steel

**FS** Strip galvanized

### Master data

Item number	6358717
Description 1	Centre suspension
Description 2	for cable tray
Manufacturer	OBO
Dimension	B300mm
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	36.7 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,9686 kg COe / 1 Piece


# Technical data sheet

## Central hanger for cable tray, side height 60 mm FS



Item number: 6358717

### Dimensions



Length	40 mm
Width	300 mm
Width	16 in
Height	57 mm
Dimension B	295 mm
Dimension b	284 mm
Dimension B1	284 mm

### Technical data

Version for	Suspended
F in kN	0.2 kN
Maintain electrical functions	no
for width max.	300 mm
for width min.	300
Suitable for metric threaded rod	10
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Suitable for tray/ladder width	300 mm
Hole diameter	10.5 mm
Adjustable	no