

Technical data sheet

Metal strip clips, narrow

Item number: 7203103



Metal strip clip in a smooth finish with ball lock. For high-temperature and weather-resistant fastening. Use spring chuck MBS-Z for tightening.

A2 Stainless steel

2B Bright, treated

Master data

Item number	7203103
Type	MBS 030 A2
Description 1	Strip clip
Manufacturer	OBO
Dimension	7,9x300
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.61 kg
Weight unit	kg/100 pc.

Dimensions

Length	300 mm
Width	7.9 mm
Height	5.5 mm
Dimension L	300 mm
Dimension t	0.25 mm

Technical data sheet

Metal strip clips, narrow

Item number: 7203103



Technical data

Version for	Without toothing
Strip closure	Ball lock
Fastening type	Without
Labelling area	Without
Halogen-free	yes
Releasable lock	no
Max. Bundle diameter	40 mm
MIL approval	no
Mounting temperature, max.	50 °C
Mounting temperature_min.	5 °C
Reflective	no
Permitted temperature range, max.	70 °C
Permitted temperature range, min.	-20 °C
Transparent	no
UL approval	no
UV-resistant	yes
VG approval	no