

Technical data sheet

Metal strip clips, wide

Item number: 7203113



Metal strip clip in a smooth finish with ball lock. For high-temperature and weather-resistant fastening. Use spring chuck MBS-Z for tightening.

A2 Stainless steel

2B Bright, treated

Master data

Item number	7203113
Type	MBS 120 A2
Description 1	Strip clip
Manufacturer	OBO
Dimension	12x1200
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	3 kg
Weight unit	kg/100 pc.

Dimensions

Length	1,200 mm
Width	12 mm
Height	6.5 mm
Dimension L	1,200 mm
Dimension t	0.25 mm

Technical data sheet

Metal strip clips, wide

Item number: 7203113



Technical data

Version for	Without toothing
Strip closure	Ball lock
Fastening type	Without
Labelling area	Without
Halogen-free	yes
Releasable lock	no
Max. Bundle diameter	175 mm
MIL approval	no
Mounting temperature, max.	50 °C
Mounting temperature_min.	5 °C
Reflective	no
Permitted temperature range, max.	70 °C
Permitted temperature range, min.	-20 °C
Transparent	no
UL approval	no
UV-resistant	yes
VG approval	no