

Technical data sheet

Base, MultiBase with remote signalling

Item number: 5096649



- Suitable for V 25-B+C, V 20-C and V10-C
- Pre-mounted and ready for connection
- Multifunction terminals for easy connection to series-mounted devices
- Upper parts can be rotated through 180 degrees
- With remote signalling, potential-free NO contact, for function monitoring



Master data		
	Item number	5096649
	Description 1	MultiBase
	Description 2	1-pole + RS
	Manufacturer	OBO
	Dimension	1-polig+FS
	Smallest sales unit	1
	Unit of quantity	Piece
	Weight	7.932 kg
	Weight unit	kg/100 pc.

Dimensions		

Technical data sheet

Base, MultiBase with remote signalling

Item number: 5096649



Technical data

Pole version	1
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	yes
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Installation type	DIN rail 35 mm
Network form	Other
Protection rating	IP20