

Technical data sheet

MultiBase base

Item number: 5096648




- Suitable for V25-B+C, V20-C and V10-C
- Pre-mounted and ready for connection
- For TN systems
- Multifunction terminals for easy circuit of series-mounted devices
- Upper parts can be rotated through 180 degrees



Master data

Item number	5096648
Description 1	MultiBase
Description 2	1-pole
Manufacturer	OBO
Dimension	1-polig
Smallest sales unit	1
Unit of quantity	Piece
Weight	9.9 kg
Weight unit	kg/100 pc.

Dimensions



Technical data sheet

MultiBase base

Item number: 5096648



Technical data

Pole version	1
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Installation type	DIN rail 35 mm
Network form	TN
Protection rating	IP20
Signalling on device	None