

Technical data sheet

MultiBase base + NPE

Item number: 5096669




- Suitable for V 25-B+C, V 20-C and V10-C
- Pre-mounted and ready for connection
- Multifunction terminals for easy connection to series-mounted devices
- Upper parts can be rotated through 180 degrees
- For TN-S and TT network systems

Master data

Item number	5096669
Type	MB 3+NPE
Description 1	MultiBase
Description 2	3-pole + NPE
Manufacturer	OBO
Dimension	3+NPE
Smallest sales unit	1
Unit of quantity	Piece
Weight	21 kg
Weight unit	kg/100 pc.

Dimensions



Technical data sheet

MultiBase base + NPE

Item number: 5096669



Technical data

Version for	3+NPE
Pole version	3+N/PE
Structural width in division units (division unit, 17.5 mm)	4
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Installation type	DIN rail 35 mm
Network form	Other
Protection rating	IP20