

Technical data sheet

Metal spreading anchor

Item number: 3484629



Areas of application: gas concrete, lightweight concrete, Poroton, pumice, plaster, hollow brick and full brick. Can be knocked into porous concrete (gas concrete) of low resistance without drilling. Superbly suited for areas subjected to high temperatures.




Steel

Electrogalvanized, transparently passivated

Master data

Item number	3484629
Description 1	Metal expanding anchor
Manufacturer	OBO
Dimension	6x32mm
Material	Steel
Surface	Electrogalvanized, transparently passivated
Surface standard	
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.25 kg
Weight unit	kg/100 pc.

Dimensions



Length	32 mm
Dimension D	6 mm
Dimension L	32 mm

Technical data sheet

Metal spreading anchor

Item number: 3484629



Technical data

Version for	Spreading anchor
Drill hole depth	38 mm
Drill hole diameter, max.	9 mm
Drill hole diameter, min.	7 mm
Suitable for fastening with cable ties	no
Suitable for gas concrete	yes
Suitable for hexagonal wood screw	no
Wood screws	5-6
With edge	no
With bolts	no
Suitable for material	Porous concrete Gas concrete Full brick Hollow brick