


Technical data sheet

Mounting plate 2 x data socket type F for System 55

Item number: 7408707



Mounting plate to accept two connection sockets for data technology, type Ava-
ya/Systimax: M series.
Dimensions of a mounting opening in mm: 17.40 x 16.60.




A2 Stainless steel

Master data

Item number	7408707
Type	MPMT45 2F
Description 1	Mounting plate
Description 2	with 2x hole pattern Type F
Manufacturer	OBO
Dimension	77x24x1,5
Material	Stainless steel
Smallest sales unit	1
Unit of quantity	Piece
Weight	1.64 kg
Weight unit	kg/100 pc.

Dimensions



Technical data sheet

Mounting plate 2 x data socket type F for System 55

Item number: 7408707



Technical data

Connection options	2 connection sockets for data technology, type Avaya/Systimax: M series
Fastening type	Lockable
Labelling panel	no
Floor covering protection frame	no
Floor plate	no
Lowerable to be flush-floor	no
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	no
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	yes
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	yes
Suitable for underfloor ducts	yes
With floor covering recess	no
Heavy-duty version	no
Strain relief option	yes