

# Technical data sheet

MS4022 mounting rail, heavy duty, slot 18 mm, A2, perforated

Item number: 1121960



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



A2	Stainless steel
2B	Bright, treated

Master data		
Item number	1121960	
Type	MS4022P2000A2	
Description 1	Profile rail	
Description 2	perforated, slot 18mm	
Manufacturer	OBO	
Dimension	2000x40x22,5	
Material	Stainless steel	
Surface	Bright, treated	
Surface standard		
Smallest sales unit	2	
Unit of quantity	Metre	
Weight	152.5 kg	
Weight unit	kg/100 m	
CO Footprint (GWP) Cradle-to-Gate	7,6047 kg COe / 1 Meter	


# Technical data sheet

MS4022 mounting rail, heavy duty, slot 18 mm, A2, perforated

Item number: 1121960



## Dimensions



Length	2,000 mm
Width	40 mm
Height	22.5 mm
Dimension L	2,000 mm

## Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	no
Material thickness	2 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	18 mm
Static value A	1.74 cm <sup>2</sup>
Static value I <sub>y</sub>	1.18 cm
Static value I <sub>z</sub>	4.45 cm
Static value W <sub>y</sub>	1.05 cm <sup>2</sup>
Static value W <sub>z</sub>	2.23 cm <sup>2</sup>