

Technical data sheet

Hook-head screw A4

Item number: 1148164



Hook-head screw for use with MS4022 profile rail



A4 Stainless steel

2B Bright, treated

Master data

Item number	1148164
Type	MS40HB M10x60 A4
Description 1	Hook-head screw
Description 2	for profile rail MS4022
Manufacturer	OBO
Dimension	M10x60mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	7.85 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,3809 kg COe / 1 Piece


Technical data sheet

Hook-head screw A4

Item number: 1148164



Dimensions



Length	35 mm
Width	14 mm
Height	7.5 mm

Technical data

Torque	14 Nm
Suitable for mounting rail	yes
Thread	M10x60mm
Thread metric	10