

Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, perforated

Item number: 1121405



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



- St Steel
- FT Hot-dip galvanised

Master data		
Item number	1121405	
Type	MS5030P0500FT	
Description 1	Profile rail	
Description 2	perforated, slot 22mm	
Manufacturer	OBO	
Dimension	500x50x30	
Material	Steel	
Surface	Hot-dip galvanised	
Surface standard	DIN EN ISO 1461	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	141 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	3,1218 kg COe / 1 Piece	


Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, perforated

Item number: 1121405



Dimensions



Length	500 mm
Width	50 mm
Height	30 mm
Dimension L	500 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	yes
Material thickness	3 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	22 mm
Static value A	3.39 cm ²
Static value I _y	3.99 cm
Static value I _z	13.11 cm
Static value W _y	3.95 cm ²
Static value W _z	6.38 cm ²