

Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, perforated

Item number: 1121332



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	1121332
Type	MS5030P0700FT
Description 1	Profile rail
Description 2	perforated, slot 22mm
Manufacturer	OBO
Dimension	700x50x30
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	198 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	4,3826 kg COe / 1 Piece


Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, perforated

Item number: 1121332



Dimensions



Length	700 mm
Width	50 mm
Height	30 mm
Dimension L	700 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	yes
Material thickness	3 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	22 mm
Static value A	3.39 cm ²
Static value I _y	3.99 cm
Static value I _z	13.11 cm
Static value W _y	3.95 cm ²
Static value W _z	6.38 cm ²