


Technical data sheet

MS5030 mounting rail, slot 22 mm, A2, perforated

Item number: 1121480



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



A2 Stainless steel

2B Bright, treated

Master data

Item number	1121480
Type	MS5030P2000A2
Description 1	Profile rail
Description 2	perforated, slot 22mm
Manufacturer	OBO
Dimension	2000x50x30
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	2
Unit of quantity	Metre
Weight	280 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	14,4446 kg COe / 1 Meter


Technical data sheet

MS5030 mounting rail, slot 22 mm, A2, perforated

Item number: 1121480



Dimensions



Length	2,000 mm
Width	50 mm
Height	30 mm
Dimension L	2,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	no
Material thickness	3 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	18 mm
Static value A	3.39 cm ²
Static value I _y	3.99 cm
Static value I _z	13.11 cm
Static value W _y	3.95 cm ²
Static value W _z	6.38 cm ²