

Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, unperforated

Item number: 1121524



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	1121524
Type	MS5030UP2000FT
Description 1	Profile rail
Description 2	unperforated, slot 22mm
Manufacturer	OBO
Dimension	2000x50x30
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	20
Unit of quantity	Metre
Weight	307 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	6,1135 kg COe / 1 Meter


Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, unperforated

Item number: 1121524



Dimensions



Length	2,000 mm
Width	50 mm
Height	30 mm
Dimension L	2,000 mm

Technical data

Breakable	no
Type of perforation	Without
Version for	Single profile
Maintain electrical functions	no
Material thickness	3 mm
With perforation	no
With tothing	no
Profile shape	C profile
Slot width	22 mm
Static value A	1.74 cm ²
Static value I _y	1.19 cm
Static value I _z	4.46 cm
Static value W _y	1.05 cm ²
Static value W _z	2.23 cm ²