

# Technical data sheet

Audio/video cinch connection, 1 module, slanting outlet, as soldered connection, pure white

Item number: 6105174



Multimedia support with three cinch connection sockets for audio/video, slanting cable outlet, with labelling panel, three cinch sockets (RCA) with soldered connection, colour coding yellow / red / white. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate

## Master data

Item number	6105174
Type	MTS-12R L RW1
Description 1	Multimedia support audio/video
Description 2	3xsocket with sold. connection
Manufacturer	OBO
Dimension	45x45mm
Colour	Pure white; RAL 9010
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	3.4 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1068 kg CO2e / 1 Piece


# Technical data sheet

Audio/video cinch connection, 1 module, slanting outlet, as soldered connection, pure white

Item number: 6105174



## Dimensions



## Technical data

Number of units	1
Surface version	Matt
Fastening type	Lock
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	no
With dust protection	no
Protection rating	IP20
Support ring	no
Transparent	no
Use	Cinch
Strain relief option	no
Combination	Basic element with central cover plate