

Technical data sheet

USB 2.0/3.0 connection, 1 module, slanting outlet, with connection cable

Item number: 6104940



Multimedia support with one USB 3.0 connection socket, slanting cable outlet, with labelling panel, short USB 3.0 type A connection cable, socket-socket version. Support plate with locking fastening, suitable for horizontal and vertical installation in the system environment.

PC Polycarbonate

Master data

Item number	6104940
Description 1	Multimedia support,USB 3.0 A-A
Description 2	with cable, socket-socket
Manufacturer	OBO
Dimension	45x45mm
Colour	Aluminium painted
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	6.2 kg
Weight unit	kg/100 pc.


Technical data sheet

USB 2.0/3.0 connection, 1 module, slanting outlet, with connection cable

Item number: 6104940



Dimensions



Width	45 mm
Height	45 mm

Technical data

Number of units	1
Surface version	Matt
Fastening type	Lock
Labelling panel	With labelling panel
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	yes
With dust protection	no
Protection rating	IP20
Depth	26 mm
Support ring	no
Transparent	no
Use	USB
Strain relief option	no
Combination	Basic element with central cover plate