

# Technical data sheet

Trunking unit, blank, locking, height 100–150 mm

Item number: 7424504



Ready-to-mount trunking unit with three self-locking blanking covers for cable laying, consisting of the trunking base (floor trough with side and floor covering guide profiles) and trunking lid. Floor trough with holding shackles for self-contacting mounting of dividers. The scope of supply contains six height-adjustable wall fixing brackets, six screed anchors and three cover joint supports (for nominal trunking widths 200 and 300) or three height-adjustable cover joint supports (for nominal trunking widths 400, 500 and 600). Trunking lid screwed down when delivered.



St

Steel

FS

Strip galvanized

## Master data

Item number	7424504
Type	OKA-W40010050R
Description 1	Flushfloor trunking unit
Description 2	blank, locking
Manufacturer	OBO
Dimension	2400x400x100
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	2.4
Unit of quantity	Metre
Weight	1883.3 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	88,0935 kg CO2e / 1 Meter


# Technical data sheet

Trunking unit, blank, locking, height 100–150 mm

Item number: 7424504



## Dimensions



Length	2,400 mm
Width	400 mm

## Technical data

Mounting opening cover	no
Covers	3
Number of insertable partitions	2
Number of planned flush-mount units	3
Number of compartments	3 St.
Mounting system fastening type	Floor
Floor plate	yes
Cover fastening, locking	yes
Seal installation option	yes
Installation opening for on-floor tank	no
Decouplable	no
Suitable for expansion joint	no
Mesh wall	no
Trunking height, max.	150 mm
Duct height, min.	100 mm
Cover material thickness	4
Minimum screed height	100
With connection opening	no
With equipotential bonding	no
With separating retainer	no
With overhang	yes
Mounting opening	Without
Height-adjustment range, max.	150 mm
Height-adjustment range, min.	100 mm
Removable cover	yes
Separating retainer fastening	stecken
Separating retainer fastening	Plug