

Technical data sheet

Power supply for PDP-OS, 5 V

Item number: 5080452



Power supply for PDP-OS plug-in data cable protection with visual and remote signalling.

- Support of max. 25 PDP-OS
- Suitable for DIN rail mounting
- With visual signalling and option of remote signalling

Application: Universal lightning and surge protection for data transmission devices with MCR technology.



Master data		
Item number	5080452	
Description 1	Pluggable data line protection	
Description 2	power supply	
Manufacturer	OBO	
Dimension	5V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	5.8 kg	
Weight unit	kg/100 pc.	

Technical data sheet

Power supply for PDP-OS, 5 V

Item number: 5080452



Dimensions	
	Length
	75 mm
	Width
	13 mm
	Height
	98 mm

Technical data	
	Connection cross-section, flexible, max.
	1.5 mm²
	Connection cross-section, flexible, min.
	0.14 mm²
	Connection cross-section, multi-wire, max.
	2.5 mm²
	Connection cross-section, multi-wire, min.
	0.14 mm²
	Connection cross-section, rigid, max.
	2.5 mm²
	Connection cross-section, rigid, min.
	0.14 mm²
	Earthing via:
	Connection cable
Telecommunications contact	
yes	
Mounting of input / output	
Screw terminals	
Mounting type	
DIN rail 35 mm	
Shielding connection available	
no	
Protection rating	
IP20	
Signalling on device	
Visual	
Permitted temperature range, max.	
80 °C	
Permitted temperature range, min.	
-40 °C	