# Technical data sheet

### Add-on tee 60 A2

**Item number: 6042319** 



Add-on tee for the creation of a horizontal branch or cross-over, fitting for lock and screw-on cable trays of side height 60 mm. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used indoors and outdoors. Fastening material must be ordered separately.



# CECH

A2

Stainless steel

2E

Bright, treated

#### Master data

6042319
RAA 640 A2
Add-on tee
for cable tray
OBO
60x400
stainless steel
Stainless steel
Bright, treated
1
Piece
67.2 kg
kg/100 pc.
5,7985 kg CO2e / 1 Piece

## **Technical data sheet**

### Add-on tee 60 A2

**Item number: 6042319** 



Dimensions			
608	Width	400 mm	
200000000000000000000000000000000000000	Height	60 mm	
	Plate thickness	1 mm	
	Dimension B	400 mm	
E 2000000000000 E			
396			

Tec			

Departing width	400 mm
Connector version	Integrated connector
Maintain electrical functions	yes
Material thickness, floor plate	1 mm
NATO hole pattern	no
Rustproof steel, pickled	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	screwed/clamped
Recommended quantity of bolts	22 St.
Rail thickness	1.25 mm