


Technical data sheet

Add-on tee 85 FS

Item number: 6042133



Add-on tee for the creation of a horizontal branch or cross-over, fitting for lock and screw-on cable trays of side height 85 mm. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used in indoor areas. Fastening material must be ordered separately.



St Steel

FS Strip galvanized

Master data

Item number	6042133
Type	RAA 820 FS
Description 1	Add-on tee
Description 2	for cable tray
Manufacturer	OBO
Dimension	85x200
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	50.6 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,7731 kg CO2e / 1 Piece


Technical data sheet

Add-on tee 85 FS

Item number: 6042133



Dimensions



Width	200 mm
Height	85 mm
Plate thickness	0.8 mm
Dimension B	200 mm

Technical data

Departing width	200 mm
Connector version	Integrated connector
Maintain electrical functions	no
Material thickness, floor plate	0.8 mm
NATO hole pattern	no
Rustproof steel, pickled	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	screwed/clamped
Recommended quantity of bolts	16 St.
Rail thickness	1.25 mm