Technical data sheet Cover, 90° bend A4

Item number: 6036986



Cover for 90° bend fitting for lockable and screw-on cable trays in indoor and outdoor areas, to protect cables against damage and soiling. Fastening with premounted sash lock and through attachment of the section cover. Suitable for all side heights.

The cover can be used with fittings of all side heights.





2B Bright, treated

Master data

Item number	6036986
Туре	RBD 90 100 A4
Description 1	Cover
Description 2	for 90° bend
Manufacturer	OBO
Dimension	B100mm
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	15 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to- Gate	1,7472 kg CO2e / 1 Piece

Item number: 6036986



Dimensions



Length	158 mm
Width	100 mm
Plate thickness	0.75 mm
Dimension B	100 mm

Technical data

Bend (angle)	90°
Number of turn buckles	1 St.
Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Change of direction	Horizontal
Rustproof steel, pickled	no
Hinged	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C