


# Technical data sheet

## Bend, angle-adjustable, 60 A2

Item number: 6037162



Angle-adjustable bend for the creation of a horizontal branch, fitting for lock and screw-on cable trays of side height 60 mm. Adjustable angle 0–90°. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used indoors and outdoors. Fastening material must be ordered separately.



A2	Stainless steel
2B	Bright, treated

### Master data

Item number	6037162
Type	RB W 660 A2
Description 1	Adjustable bend
Description 2	horizontal
Manufacturer	OBO
Dimension	60x600
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	405.8 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	48,1341 kg CO2e / 1 Piece


# Technical data sheet

Bend, angle-adjustable, 60 A2

Item number: 6037162



## Dimensions



Width	600 mm
Height	60 mm
Plate thickness	1.25 mm
Dimension B	600 mm
Dimension L	1,050 mm
Dimension R	50 mm

## Technical data

Bend (angle)	Adjustable
Connector version	Integrated connector
Type	Adjustable bend_complete
Maintain electrical functions	no
Material thickness, floor plate	1.25 mm
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Change of direction	Horizontal
Rustproof steel, pickled	no
Side perforation	yes
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	screwed/clamped
Recommended quantity of bolts	16 St.
Rail thickness	1.25 mm