

Technical data sheet

Round conductor, stainless steel A2

Item number: 5021235



- Can be used as a conductor according to DIN EN 62561-2 (VDE 0185-561-2)
- Corresponds to the requirements of VDE 0185-305 (IEC 62305)
- RD 10-V4A for applications in the earth
- According to the foundation earth electrode standard DIN 18014, V4A is required in the earth



A2 Stainless steel

Master data

Item number	5021235
Type	RD 8-V2A
Description 1	Round conductors
Description 2	50 kg ring
Manufacturer	OBO
Dimension	8mm
Material	Stainless steel
Smallest sales unit	125
Unit of quantity	Metre
Weight	40 kg
Weight unit	kg/100 m


Technical data sheet

Round conductor, stainless steel A2

Item number: 5021235



Dimensions



Dimension D	8 mm
-------------	------

Technical data

Number of individual wires	1
High voltage-resistant, insulated version	no
Normal ring (ca. kg)	50
Normal ring (approx. m)	125
Length tolerance $\pm$	5 %
Cross-section	50 mm ²
Material property	Miscellaneous
Material jacket	Without