


Technical data sheet

Adjustable bend element, vertical 60 A2

Item number: 7075651



Adjustable vertical bend element, for all cable tray types with a side height of 60 mm.
RGV 60 adjustable connectors should be ordered separately and in the appropriate quantity.
Please order RGV 60 and SKS 8x16 hexagonal bolts separately.



A2	Stainless steel
2B	Bright, treated

Master data

Item number	7075651
Type	RGBEV 610 A2
Description 1	Adjustable bend element
Description 2	vertical
Manufacturer	OBO
Dimension	60x100
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	53.3 kg
Weight unit	kg/100 pc.

Dimensions

Width	100 mm
Height	60 mm
Plate thickness	1 mm
Dimension B	100 mm

Technical data sheet

Adjustable bend element, vertical 60 A2

Item number: 7075651



Technical data

Bend (angle)	Adjustable
Connector version	Without connectors
Type	Adjustable bend element
Maintain electrical functions	no
Mounting perforation in base	no
NATO hole pattern	no
Change of direction	Vertical, rising/falling
Rustproof steel, pickled	no
Side perforation	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	Screwed