

Technical data sheet

90° adjustable bend, vertical 110 FS

Item number: 7006683



90° adjustable vertical bend, for all cable tray types with a side height of 110 mm. The bend is shipped in an unmounted state. No additional fastening materials are required.



St	Steel
FS	Strip galvanized

Master data

Item number	7006683
Description 1	Adjustable bend
Description 2	vertical
Manufacturer	OBO
Dimension	110x400
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	530 kg
Weight unit	kg/100 pc.

Dimensions

Width	400 mm
Width	16 in
Height	110 mm
Height	4 in
Plate thickness	1 mm
Dimension R	400 mm

Technical data sheet

90° adjustable bend, vertical 110 FS

Item number: 7006683



Technical data

Bend (angle)	90°
Connector version	Supplied connectors
Type	Adjustable bend_complete
Maintain electrical functions	no
Mounting perforation in base	no
NATO hole pattern	no
Change of direction	Vertical, rising/falling
Rustproof steel, pickled	no
Side perforation	no
Wide-span version	no
Type of connector, cable support system	Screwed