

# Technical data sheet

## 90° adjustable bend, vertical 60 FS

Item number: 7006365



90° adjustable vertical bend, for all cable tray types with a side height of 60 mm. The bend is shipped in an unmounted state. No additional fastening materials are required.



St

Steel

FS

Strip galvanized

### Master data

|                     |                  |
|---------------------|------------------|
| Item number         | 7006365          |
| Description 1       | Adjustable bend  |
| Description 2       | vertical         |
| Manufacturer        | OBO              |
| Dimension           | 60x300           |
| Colour              | zinc             |
| Material            | Steel            |
| Surface             | Strip galvanized |
| Surface standard    | DIN EN 10346     |
| Smallest sales unit | 1                |
| Unit of quantity    | Piece            |
| Weight              | 260 kg           |
| Weight unit         | kg/100 pc.       |

### Dimensions

|                 |        |
|-----------------|--------|
| Width           | 300 mm |
| Width           | 12 in  |
| Height          | 60 mm  |
| Height          | 2 in   |
| Plate thickness | 1 mm   |
| Dimension R     | 400 mm |

# Technical data sheet

90° adjustable bend, vertical 60 FS

Item number: 7006365



## Technical data

|                                         |                          |
|-----------------------------------------|--------------------------|
| Bend (angle)                            | 90°                      |
| Connector version                       | Supplied connectors      |
| Type                                    | Adjustable bend_complete |
| Maintain electrical functions           | no                       |
| Mounting perforation in base            | no                       |
| NATO hole pattern                       | no                       |
| Change of direction                     | Vertical, rising/falling |
| Rustproof steel, pickled                | no                       |
| Side perforation                        | no                       |
| Wide-span version                       | no                       |
| Type of connector, cable support system | Screwed                  |