

Technical data sheet


Adjustable connector 110 FT

Item number: 7082436



Adjustable connector for cable trays with a side height of 110 mm.

Including appropriate fastening material.



- St

Steel
- FT

Hot-dip galvanised

Master data

Item number	7082436
Type	RGV 110 FT
Description 1	Adjustable connector
Description 2	for cable tray
Manufacturer	OBO
Dimension	110x300
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	10
Unit of quantity	Piece
Weight	64.3 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,6443 kg CO2e / 1 Piece


Technical data sheet

Adjustable connector 110 FT

Item number: 7082436



Dimensions



Dimension	300 x 106
Length	300 mm
Width	16 mm
Height	110 mm
Height	4 in
Plate thickness	2 mm

Technical data

Version for	Straight connector
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Suitable for cable tray system height	110 mm
Adjustable connector, horizontal	no
Articulated connector, vertical	yes
Rustproof steel, pickled	no
Connection type	Screw connector
Wide-span version	no