

Technical data sheet

Cover, cross-over 500 A2

Item number: 7027868



Cover for cross-over fitting for lockable and screw-on cable trays in indoor and outdoor areas, to protect cables against damage and soiling. Fastening through attachment of the section cover. Suitable for all side heights. The cover can be used with fittings of all side heights.



- A2 Stainless steel
- 2B Bright, treated

Master data	
Item number	7027868
Type	RKD 500 A2
Description 1	Cover
Description 2	for cross-over
Manufacturer	OBO
Dimension	B500mm
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	294 kg
Weight unit	kg/100 pc.


Technical data sheet

Cover, cross-over 500 A2

Item number: 7027868



Dimensions



Width	500 mm
Plate thickness	1 mm
Dimension B	500 mm

Technical data

Number of turn buckles	0 St.
Fastening type	On top
Suitable for cable ladder	no
Suitable for cable tray	yes
Rustproof steel, pickled	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C