


Technical data sheet

Cross-over 110 FS

Item number: 7027363



Cross-over for the creation of a horizontal branch, fitting for lock and screw-on cable trays of side height 110 mm. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used in indoor areas. Fastening material must be ordered separately.



St Steel

FS Strip galvanized

Master data

Item number	7027363
Type	RK 160 FS
Description 1	Cross over
Description 2	for cable tray
Manufacturer	OBO
Dimension	110x600
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	565 kg
Weight unit	kg/100 pc.


Technical data sheet

Cross-over 110 FS

Item number: 7027363



Dimensions



Width	600 mm
Height	110 mm
Plate thickness	1 mm
Dimension B	600 mm
Dimension R	50 mm

Technical data

Connector version	Integrated connector
Maintain electrical functions	no
Material thickness, floor plate	1 mm
NATO hole pattern	no
Rustproof steel, pickled	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	screwed/clamped
Recommended quantity of bolts	48 St.
Rail thickness	1.25 mm