


Technical data sheet

Cross-over 85 FS

Item number: 7027331



Cross-over for the creation of a horizontal branch, fitting for lock and screw-on cable trays of side height 85 mm. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used in indoor areas. Fastening material must be ordered separately.



St

Steel

FS

Strip galvanized

Master data

Item number	7027331
Type	RK 810 FS
Description 1	Cross over
Description 2	for cable tray
Manufacturer	OBO
Dimension	85x100
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	108.5 kg
Weight unit	kg/100 pc.


Technical data sheet

Cross-over 85 FS

Item number: 7027331



Dimensions



Width	100 mm
Height	85 mm
Plate thickness	0.8 mm
Dimension B	100 mm
Dimension R	50 mm

Technical data

Connector version	Integrated connector
Maintain electrical functions	no
Material thickness, floor plate	0.8 mm
NATO hole pattern	no
Rustproof steel, pickled	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	screwed/clamped
Recommended quantity of bolts	28 St.
Rail thickness	1.25 mm