


Technical data sheet

Cross-over 85 FT

Item number: 7027435



Cross-over for the creation of a horizontal branch, fitting for lock and screw-on cable trays of side height 85 mm. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used indoors and outdoors. Fastening material must be ordered separately.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	7027435
Type	RK 830 FT
Description 1	Cross over
Description 2	for cable tray
Manufacturer	OBO
Dimension	85x300
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	255.9 kg
Weight unit	kg/100 pc.


Technical data sheet

Cross-over 85 FT

Item number: 7027435



Dimensions



Width	300 mm
Height	85 mm
Plate thickness	1 mm
Dimension B	300 mm
Dimension R	50 mm

Technical data

Connector version	Integrated connector
Maintain electrical functions	no
Material thickness, floor plate	1 mm
NATO hole pattern	no
Rustproof steel, pickled	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	screwed/clamped
Recommended quantity of bolts	36 St.
Rail thickness	1.25 mm