

Technical data sheet


Reducer/stop-end 60 A4

Item number: 7109961



Reducer and end closure plate for cable trays with side height 60 mm.
From a width of 150 mm, a perforated lower flange is available.

Including appropriate fastening material.



A4 Stainless steel

2B Bright, treated

Master data

Item number	7109961
Type	RWEB 660 A4
Description 1	Reducer profile/end closure
Description 2	for cable tray
Manufacturer	OBO
Dimension	60x600
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	57.4 kg
Weight unit	kg/100 pc.


Technical data sheet

Reducer/stop-end 60 A4

Item number: 7109961



Dimensions



Width	600 mm
Height	60 mm
Height	2 in
Plate thickness	1 mm
Dimension B	595 mm

Technical data

Connector version	Integrated connector
Maintain electrical functions	no
Rustproof steel, pickled	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no