

# Technical data sheet

## Stainless steel pipe, V4A

Item number: 2046753



Electrical installation pipe without threaded ends to EN 61386-1 for mechanical protection of cables. With burr-free inner wall. Corrosion protection class 4 (high).



- A4 Stainless steel
- 2B Bright, treated

| Master data                       |                         |
|-----------------------------------|-------------------------|
| Item number                       | 2046753                 |
| Type                              | S32W A4                 |
| Description 1                     | Stainless steel pipe    |
| Description 2                     | without thread          |
| Manufacturer                      | OBO                     |
| Dimension                         | Ø32, 3000mm             |
| Material                          | Stainless steel         |
| Surface                           | Bright, treated         |
| Surface standard                  |                         |
| Smallest sales unit               | 15                      |
| Unit of quantity                  | Metre                   |
| Weight                            | 91.2 kg                 |
| Weight unit                       | kg/100 m                |
| CO Footprint (GWP) Cradle-to-Gate | 1,4745 kg COe / 1 Meter |

# Technical data sheet

Stainless steel pipe, V4A

Item number: 2046753



## Dimensions

|                  |          |
|------------------|----------|
| Length           | 3,000 mm |
| Dimension D      | 32 mm    |
| Dimension L      | 3,000 mm |
| Dimension m (mm) | M32      |
| Dimension t      | 1.2 mm   |



3000

# Technical data sheet

## Stainless steel pipe, V4A

Item number: 2046753



### Technical data

|                                                |                         |
|------------------------------------------------|-------------------------|
| Surface-mounted                                | yes                     |
| Pipe version                                   | Rigid without thread    |
| Concrete installation                          | yes                     |
| Bending behaviour                              | rigid                   |
| Pressure resistance                            | Very heavy (4,000 N)    |
| Use temperature, max.                          | + 400 °C                |
| Use temperature, min.                          | - 45 °C                 |
| Cavity wall installation                       | yes                     |
| Installation on wood                           | yes                     |
| Installation in the earth                      | yes                     |
| Installation outdoors                          | yes                     |
| Classification code                            | 55571                   |
| Machines and system installation               | yes                     |
| Brushed surface                                | yes                     |
| Polished surface                               | no                      |
| Impact resistance                              | Very heavy (6.8/300 mm) |
| Permitted temperature range, max.              | 400 °C                  |
| Permitted temperature range, min.              | -45 °C                  |
| Underfloor installation (bitumen, hot asphalt) | yes                     |
| Underfloor installation (screed)               | yes                     |
| Concealed                                      | yes                     |