

Technical data sheet

Stainless steel pipe, V4A

Item number: 2046756



Electrical installation pipe without threaded ends to EN 61386-1 for mechanical protection of cables. With burr-free inner wall. Corrosion protection class 4 (high).



A4 Stainless steel

2B Bright, treated

Master data

Item number	2046756
Type	S63W A4
Description 1	Stainless steel pipe
Description 2	without thread
Manufacturer	OBO
Dimension	Ø63, 3000mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	9
Unit of quantity	Metre
Weight	227.5 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	3,6542 kg COe / 1 Meter

Technical data sheet

Stainless steel pipe, V4A

Item number: 2046756



Dimensions

Length	3,000 mm
Dimension D	63 mm
Dimension L	3,000 mm
Dimension m (mm)	M63
Dimension t	1.5 mm



Technical data sheet

Stainless steel pipe, V4A

Item number: 2046756



Technical data

Surface-mounted	yes
Pipe version	Rigid without thread
Concrete installation	yes
Bending behaviour	rigid
Pressure resistance	Very heavy (4,000 N)
Use temperature, max.	+ 400 °C
Use temperature, min.	- 45 °C
Cavity wall installation	yes
Installation on wood	yes
Installation in the earth	yes
Installation outdoors	yes
Classification code	55571
Machines and system installation	yes
Brushed surface	yes
Polished surface	no
Impact resistance	Very heavy (6.8/300 mm)
Permitted temperature range, max.	400 °C
Permitted temperature range, min.	-45 °C
Underfloor installation (bitumen, hot asphalt)	yes
Underfloor installation (screed)	yes
Concealed	yes