

Technical data sheet

Stainless steel pipe bend, V4A

Item number: 2046764



90° bend with moulded sleeves, for electrical installation pipes according to EN 61386-1. With burr-free inner wall.



A4 Stainless steel

2B Bright, treated

Master data

Item number	2046764
Type	SB40W A4
Description 1	Stainless steel bend
Description 2	without thread
Manufacturer	OBO
Dimension	Ø40mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	5
Unit of quantity	Piece
Weight	61.2 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	3,786 kg COe / 1 Piece


Technical data sheet

Stainless steel pipe bend, V4A

Item number: 2046764



Dimensions



Dimension A	50 mm
Dimension B	279 mm
Dimension D	42.7 mm
Dimension d	40.2 mm
Dimension l	40 mm
Dimension m (mm)	M40
Dimension R	170 mm
Dimension t	1.25 mm

Technical data

Version for	Connector
Flexible	no
For nominal pipe diameter	40 mm
Halogen-free	no
With inspection opening and lid	no
With sleeve	yes
Brushed surface	yes
Polished surface	no
Permitted temperature range, max.	400 °C
Permitted temperature range, min.	-45 °C
Angle of the bend	90 °
Two-part	no