

Technical data sheet

Black powder-coated steel bend, without thread

Item number: 2046825



90° bend with moulded sleeves, for electrical installation pipes according to EN 61386-1. With burr-free inner wall.



St	Steel
PE50	PES50 - Polyester/epoxy

Master data

Item number	2046825
Type	SBN20 SW
Description 1	Conduit plug-in bend
Description 2	without thread
Manufacturer	OBO
Dimension	Ø20mm
Colour	Jet black; RAL 9005
Material	Steel
Surface	PES50 - Polyester/epoxy
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	13.3 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,4103 kg COe / 1 Piece


Technical data sheet

Black powder-coated steel bend, without thread

Item number: 2046825



Dimensions



Dimension A	53.7 mm
Dimension B	155 mm
Dimension D	22.6 mm
Dimension d	20.6 mm
Dimension l	30 mm
Dimension m (mm)	M20
Dimension R	90 mm
Dimension t	1 mm

Technical data

Version for	Connector
Flexible	no
For nominal pipe diameter	20 mm
Halogen-free	no
With inspection opening and lid	no
With sleeve	yes
Brushed surface	no
Polished surface	no
Angle of the bend	90 °
Two-part	no