


Technical data sheet

Distribution box, 3 division units, empty, polycarbonate

Item number: 2008860



Small distributor for surface mounting, for the current sub-distribution in interior and exterior areas, according to IEC 439-3. With pre-mounted 35 mm hat profile rail. IP66 protection type and IK08 protection rating. Transparent cover to screw on, with cut-out. Including 4 screw cover caps.

- Protection-insulated for a maximum of 3 division units
 - 2 break-out openings each of Ø 20 mm at the top and bottom
 - 1 combination break-out opening each of Ø 20/25 mm at the top and bottom
 - 4 screw cover caps
- Nominal current 40 A
Power loss at 40 K 17 W
Measured voltage Un: 400 V
Operating measured voltage Ue: 400 V
Impulse current resistance Cat.III Uimp: 4 kV



PC Polycarbonate

Master data

Item number	2008860
Type	SDB 03L PC
Description 1	Small distributor
Description 2	no terminal strip, for 3 units
Manufacturer	OBO
Dimension	150x190x125
Colour	Light grey; RAL 7035
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	78 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	2,7558 kg COe / 1 Piece


Technical data sheet

Distribution box, 3 division units, empty, polycarbonate

Item number: 2008860



Dimensions



Length	191 mm
Width	151 mm
Height	126 mm

Technical data

Extension option	yes
Number of rows	1
Cover type	Cover
Version, small distributor cover	With cut-out
DIN rail	yes
Installation location	Internal
EMC version	no
Glow wire test	850 °C
With mounting plate	no
With lock	no
Mounting type, consumer units	Structure
Nominal insulating voltage AC	1000 V
Nominal insulating voltage DC	1500 V
Nominal voltage	400 V
Nominal current	40 A
Protection rating	IP66
Protection rating IK code	IK08
Transparent lid	yes