

# Technical data sheet

## Hexagonal bolt M10 A2

Item number: 3160798



Hexagonal bolt for universal fastening of construction components. With hexagonal nut and 2 washers.




A2	Stainless steel
2B	Bright, treated

### Master data

Item number	3160798
Type	SKS 10x190 A2
Description 1	Hexagonal screw
Description 2	with nut and washers
Manufacturer	OBO
Dimension	M10x190
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	20
Unit of quantity	Piece
Weight	14.11 kg
Weight unit	kg/100 pc.

### Dimensions



Length	190 mm
Dimension d	10 mm
Dimension L	190 mm

# Technical data sheet

## Hexagonal bolt M10 A2

Item number: 3160798



### Technical data

Resistance grade	A2-70
Thread	M 10 x 190
Thread metric	10
Thread type	Metric
Thread length	190 mm
Thread increase	1.5 mm
Head shape	Hexagonal
With flange	no
With nut	yes
With washer	yes
WAF	17
Screw system	Hexagonal
Self-locking	no
Full thread	yes
Left thread	no