


# Technical data sheet

## Cable tray SKS 85 FS

Item number: 6058302



SKS 85 = heavy-duty cable tray system with 85 mm side height.  
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



|           |                  |
|-----------|------------------|
| <b>St</b> | Steel            |
| <b>FS</b> | Strip galvanized |

### Master data

|                                   |                          |
|-----------------------------------|--------------------------|
| Item number                       | 6058302                  |
| Type                              | SKS 830 FS               |
| Description 1                     | Cable tray SKS           |
| Description 2                     | perforated               |
| Manufacturer                      | OBO                      |
| Dimension                         | 85x300x3000              |
| Colour                            | zinc                     |
| Material                          | Steel                    |
| Surface                           | Strip galvanized         |
| Surface standard                  | DIN EN 10346             |
| Smallest sales unit               | 3                        |
| Unit of quantity                  | Metre                    |
| Weight                            | 529.1 kg                 |
| Weight unit                       | kg/100 m                 |
| CO Footprint (GWP) Cradle-to-Gate | 13,9167 kg COe / 1 Meter |


# Technical data sheet

## Cable tray SKS 85 FS

Item number: 6058302



### Dimensions



|                 |          |
|-----------------|----------|
| Dimension       | 85 x 300 |
| Length          | 3,000 mm |
| Length          | 10 ft    |
| Width           | 300 mm   |
| Width           | 12 in    |
| Height          | 85 mm    |
| Height          | 3 in     |
| Plate thickness | 0.6 in   |
| Plate thickness | 1.5 mm   |
| Dimension B     | 300 mm   |
| Maß W           | 300 mm   |

### Technical data

|                                         |                       |
|-----------------------------------------|-----------------------|
| Connector version                       | Supplied connectors   |
| Mounting system fastening type          | Floor Ceiling Wall    |
| Walkable                                | no                    |
| Maintain electrical functions           | no                    |
| With cover                              | no                    |
| Mounting perforation in base            | yes                   |
| NATO hole pattern                       | no                    |
| Usable cross-section                    | 253 cm <sup>2</sup>   |
| Usable cross-section                    | 25300 mm <sup>2</sup> |
| Rustproof steel, pickled                | no                    |
| Side perforation                        | yes                   |
| Wide-span version                       | no                    |
| Load test type according to IEC 61537   | Type II               |
| Type of connector, cable support system | Screwed               |

# Technical data sheet


## Cable tray SKS 85 FS

Item number: 6058302



### Loads

|                                   |           |
|-----------------------------------|-----------|
| Insertable support spacings, min. | 1.5 m     |
| Insertable support spacings, max. | 3 m       |
| Support spacing 1.5 m             | 2.8 kN/m  |
| Support spacing 2.0 m             | 2.25 kN/m |
| Support spacing 2.5 m             | 1.5 kN/m  |
| Support spacing 3.0 m             | 0.75 kN/m |



### Load diagram, cable tray, type SKS 85

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width