


Technical data sheet

Hexagonal bolt M8 F

Item number: 3158632



Hexagonal bolt for universal fastening of construction components. With hexagonal nut and 2 washers.



St	Steel
F	Hot galvanized

Master data

Item number	3158632
Type	SKS 8x20 F
Description 1	Hexagonal screw
Description 2	with nut and washers
Manufacturer	OBO
Dimension	M8x20
Colour	zinc
Material	Steel
Surface	Hot galvanized
Surface standard	DIN 267, Teil 10
Smallest sales unit	50
Unit of quantity	Piece
Weight	1.837 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0529 kg COe / 1 Piece


Technical data sheet

Hexagonal bolt M8 F

Item number: 3158632



Dimensions



Length	20 mm
Dimension d	8 mm
Dimension L	20 mm

Technical data

Resistance grade	8.8
Thread	M 8 x 20
Thread metric	8
Thread type	Metric
Thread length	20 mm
Thread increase	1.25 mm
Head shape	Hexagonal
With nut	yes
With washer	yes
WAF	13
Screw system	Hexagonal
Self-locking	no
Full thread	yes
Left thread	no