

Technical data sheet

Vertical ladder, SLM50

Item number: 6010004



Heavyweight vertical ladder system for the maintenance of electrical function to DIN 4102 Part 12. Approved clips, type BS-U1-M-... FT. Supplied unmounted. Rungs, type C 40/..., and bolts, type FRS 8 x 35, are supplied unmounted with rail profiles. Rung distance: 300 mm

St	Steel
FT	Hot-dip galvanised

Master data

Item number	6010004
Type	SLM50C40F 20 FT
Description 1	Vertical ladder
Description 2	rung distance 300 mm
Manufacturer	OBO
Dimension	200x3000mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	628.333 kg
Weight unit	kg/100 m

Technical data sheet

Vertical ladder, SLM50

Item number: 6010004



Dimensions

18
2
40
22.5
50
2.5
200
50
25
50
11x30
176.5
300
50

Length	3,000 mm
Width	200 mm
Height	50 mm
Dimension B	200 mm
Rung slot dimension	2.00

Technical data	
Side wall version	Profile (open)
Version of the rungs	Profile unperforated
Maintain electrical functions	yes
Rustproof steel, pickled	no
Side perforation	yes
Rung distance	300 mm