

Technical data sheet

Vertical ladder, SLS80

Item number: 6010105



Industrial vertical ladder system for the maintenance of electrical function to DIN 4102 Part 12. Approved clips, type BS-U1-M-... FT. Supplied unmounted. Rung distance 300 mm. Rungs, type CK 40/..., and bolts, type FRS 10 x 25 FT, are supplied unmounted with rail profiles.

St	Steel
FT	Hot-dip galvanised

Master data

Item number	6010105
Description 1	Vertical ladder
Description 2	rung distance 300 mm
Manufacturer	OBO
Dimension	400x3000mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	1487 kg
Weight unit	kg/100 m


Technical data sheet

Vertical ladder, SLS80

Item number: 6010105



Dimensions



Length	3,000 mm
Width	400 mm
Height	80 mm
Dimension B	400 mm
Rung slot dimension	2.00

Technical data

Side wall version	Profile (open)
Version of the rungs	Profile unperforated
Maintain electrical functions	yes
Rustproof steel, pickled	no
Side perforation	yes
Rung distance	300 mm