

Technical data sheet

Coupling SL KUP20110

Item number: 6132235



Trunking coupling for SL, SL-L and SL-T skirting trunking. For connecting the interfaces of the individual trunking covers.
Easily attached using moulded snap-in hooks.



PVC Polyvinylchloride

Master data

Item number	6132235
Description 1	Coupling
Description 2	SL 20x110 9010
Manufacturer	OBO
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	0.71 kg
Weight unit	kg/100 pc.


Technical data sheet

Coupling SL KUP20110


Item number: 6132235



Dimensions



Length	24 mm
Height	110 mm



Technical data sheet

Coupling SL KUP20110

Item number: 6132235



Technical data

Decoration	Without
Cover sealing lip	Without
Halogen-free	no
Protection rating	IP40
Protection rating IK code	IK06
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C