

Technical data sheet

Connector part 3-pin, spring power connection, black

Item number: 6108050



Connector part, 3-pin, type GST18i with spring power connection for rigid cables of 1.5–2.5 mm², single-wire and ultrasonically welded, fine wire cables 1.5 mm² with end sleeves, unmounted with strain relief, can be terminated in situ, 250 V, 16 A.

Two connections per pole, for cables H05VV, NYM (Ø 7.8–10.33 mm), lockable, a lock should be provided for strain relief according to VDE 0628.

Stripping length: 45 mm

Stripped length: 9 mm



Master data

Item number	6108050
Description 1	Plug 3-pole,
Description 2	screwless connection
Manufacturer	OBO
Colour	Black
Smallest sales unit	1
Unit of quantity	Piece
Weight	2.6 kg
Weight unit	kg/100 pc.

Dimensions

